

LioN-Link The Modular, Fieldbus Independent I/O System



Optimization of Field Wiring Through the Utilization of a Modular IP 67 Fieldbus Solution





About Belden®

Effective Signal Transmission Solutions

At Belden, our customers and their requirements are our top priority. All of our leading brands – Belden®, Hirschmann™ and Lumberg Automation™ – enjoy an excellent reputation for quality and added value in their respective core markets.

The combination of proven experience and innovation behind these brands has made Belden the largest provider of an integrated range of wired and wireless systems.

Belden offers an extensive product range, including cables, connectors, I/O modules and networking components. Thanks to cooperation between our brands, we are able to provide complete signal transmission solutions from a single source with worldwide market access and delivery.

Products, People and Performance

Our extensive product range means we can deliver complete solutions backed up by comprehensive technical services. We can provide consultation, development, design and training to meet your standards and expectations.

We work with qualified partners and local experts to ensure that our world class products integrate seamlessly into your applications, helping you to achieve the best possible performance and added value.

Connectivity Solutions for Automation Technology

The Lumberg Automation™ and Hirschmann™ brands are synonymous with high quality connectors and innovative wiring solutions for use in virtually all areas of automation. Our customers use Lumberg Automation™ and Hirschmann™ products in machine building and plant engineering, building wiring installation and photovoltaic applications.

The product portfolio for these two brands comprises a wide range of connectors for sensors and actuators, single and double ended cordsets as well as distribution systems and I/O modules for connection to fieldbus and Ethernet networks.

Thanks to many years of close cooperation with system integrators and end customers in the machine building market, Lumberg Automation™ is able to deliver customized solutions using a wide range of products designed according to the latest market standards and leading edge technologies.

Lumberg Automation™ and Hirschmann™ products are renowned for their high mechanical and electrical loading capacity, excellent chemical resistance and ease of use.


Together, Lumberg Automation™ and Hirschmann™ are among Europe's leading suppliers of connectors and wiring solutions for automation technology.

Contents	2
Contents	Page
From the Oak Proofs Building to the USB List Orandon	
From the Solution of a Problem to the LioN-Link Standard	4-6
LioN-Link Wiring	7–8
Effective Connectivity Solutions	9-12
Advantages of the LioN-Link System	13
Technical Data	14-57
Wiring Accessories BusHead and I/O Modules	58-60
willing Accessories dustreau and 170 modules	30-00
LioN-Link Configurator	61
Index	62
General Technical Information	63



From the Solution of a Problem to the LioN-Link Standard

Lumberg Automation™ offers effective connectivity solutions for demanding applications at field level.



The LioN-Link decentralized I/O fieldbus system, which can be used to create line topologies of up to 100 meters in length, consists of bus coupler modules, which function as the interface to higher level fieldbuses such as **Profibus**, **CANopen®**, **DeviceNet or ProfiNet**, and **protocol independent I/O modules**.

Engineers therefore only have to make minimal changes to the hardware if their end customers use different transmission protocols for the connection of systems to their communications network. Only the BusHead requires an address setting, the fieldbus independent I/O modules are commissioned without module addressing. Furthermore, a terminator is not required in either link line. Both features contribute to protection against manipulation.

The bus coupler and I/O modules, whose connections are designed for M12 or M8 connectors, are easy to install and commission thanks to the plug and play principle. They also offer comprehensive diagnostics options, meet the requirements for **degree of protection IP 67** and have high vibration and shock resistance. Lumberg Automation™ fieldbus systems are thus ideal for use in extreme environments.

The LioN-Link I/O fieldbus system not only facilitates secure data communication, but also contributes to the **efficient operation** of machines and systems, however the field wiring may look. With LioN-Link it is always possible to implement customized solutions. The system offers a high degree of flexibility, which is very useful in the planning phase and during subsequent retrofitting or conversion. It also helps to reduce power consumption.

LioN-Link offers a complete range of connection components at field level. These include components for the control of electric drives, the networking of intelligent sensors and actuators (e.g. proximity switches, motor starters and valves), straightforward retrofitting/conversion of machines, safety applications and decentralized power supplies.


















Close to a Process


All LioN-Link modules are compliant with the IP 67 protection standard and are vibration and shock proof, which means that they can be used close to the process directly at field level.

Thanks to an innovative technological development, the complete production process can be carried out without encapsulation, making LioN-Link modules ideal for use in the smallest handling robots due to their low weight.

Universal I/O Functionality

No matter what the final design of your field wiring may be, a single I/O module is all you need to realize a whole range of different configurations. Each signal pin can be used as both an input and an output – without any additional configuration.

This gives you maximum flexibility when it comes to planning, making changes during commissioning and when retrofitting at a later date.



Quick, Fast and Easy Installation

Thanks to the staggered arrangement of the ports and the optimization of the distance between the ports, it is easy to screw on both molded and field attachable connectors. The LioN-Link modules are designed for both rear and lateral installation and can even be attached directly to profile rails.



Color Coding

Thanks to the color coding of the individual plug connections, the function of the plug-in position can be recognized directly at first glance (fieldbus, link, power supply or I/O). This allows you to quickly attach the connection cable you need.

Color	Function			
Purple	Profibus bus connection			
Black	CANopen®/DeviceNet bus connection			
Green	ProfiNet			
Orange	LioN-Link connection			
Grey	Power supply connection			



Easy Wiring with Standard Connectors

Thanks to the utilization of standard components you are also assured of uninterrupted procurement and individual part inventory availability. All of the connectors and cables necessary for the LioN-Link system can be acquired anywhere in the world.

Standard M12 connectors are used exclusively for fieldbus and link, standard M8/M12 connectors for the coupling of the sensors and actuators and standard M12/7/8" connectors for the power supply.

Advantages

- Reduced variety of part types
- Easy worldwide procurement

Link Wiring with:










LioN-Link Wiring, Ideal for Large I/O Expansion

Effective Connectivity Solutions with the LioN-Link Power Module



The LioN-Link 0941 UNC 601/...M power module is used for decentralized power supply for I/O modules. It has four ports, two potential circuits and a 10 m lead with a conductor gauge of 5x1 mm². This provides for bridging distances of up to 25 m without voltage loss as well as for configuring separate potential groups each with their own fuses.






Effective Connectivity Solutions with LioN-Link Support for I/O-Link: 0940 PSL 602/0940 ESL 601 and 0942 UEM 620

A strong Connection with LioN-Link and I/O-Link

From a user perspective, the issue of the wiring of analog signals in machines and systems has always been problematic due to the use of shielded connection cables. Although the processability of the various components such as cables and connectors has improved significantly in recent years, the assembly of a shielded cable still remains quite an elaborate procedure.

Lumberg Automation™ offers an effective solution to this problem. Thanks to the integration of an I/O-Link interface into the LioN-Link system in conjunction with I/O-Link capable sensors, users can now utilize standard wiring components such as unshielded M12 connection cables to set up the connection.



The 0942 UEM 620 I/O-Link master module provides point-to-point connections for the intelligent sensors and actuators by means of the I/O-Link protocol. The four ports can be configured as digital I/Os or for communications mode. The module is wired with three-conductor, unshielded standard cords that can be up to 20 m in length. The PROFIBUS bus coupler module allows users to connect up to six master modules. In combination with a PROFINET bus coupler module from the LioN-Link family, the I/O-Link master module can also be used in Ethernet networks.

LioN-Link ProfiNet BusHead

Lumberg Automation™ has developed a new bus coupler with PROFINET interface for the modular, decentralized LioN-Link system. This bus coupler has an integrated switch, which allows wiring of the PROFINET network in the line structure familiar from PROFIBUS networks.

There is also an integrated web server, which can be accessed via a standard TCP/IP connection. With this connection, various information can be retrieved and settings can be adjusted using a standard web browser. In addition to retrieving device information, it is also possible to set IP addresses directly. Diagnostic data for the connected LioN-Link I/O modules is also displayed, as is status information. The integration of a monitoring function facilitates the checking of the sensors and actuators connected to the I/O modules. This is facilitated by the graphical representation of the LioN-Link system structure in the web browser.

These useful tools make the system much easier to use, particularly with regard to commissioning, installation and maintenance.


Effective Connectivity Solutions with LioN-Link. Outputs for Safety Critical Applications with 0942 UEM 612

The 0942 UEM 612 I/O module is suitable for intrinsically safe actuator control or reliable emergency power off functions. It has four digital outputs for increased output current limiting of 2 A per line and a maximum total of 6 A. The module has outputs that are designed for safety critical applications up to Performance Level D of the new machinery directive.













Effective Connectivity Solutions with LioN-Link Shadow Mode: 0940 PSL 603 and 0942 UEM 620

Customized Solutions for High Flexibility

The 0940 PSL 603 bus coupler module permits the integration of up to 30 shadow modules in a Profibus network. Serving as inactive secondary components, these modules each provide eight digital I/O connections.


They can be activated by means of a hot plug function without compromising the higher level Profibus communication. In this way, systems can be retrofitted or upgraded when in operation and without the need for additional hardware.

The Lumberg Automation™ shadow module supports the management of just one, dynamically adaptable, but downwards compatible control software over the entire life cycle or plant manufacture cycle. Retaining the created hardware configuration and control program, it is possible to configure any assembly line individually in accordance with the equipment level.

Partial assembly of the sub bus system (due to different equipment levels) does not lead to a bus error. I/O modules that exist logically, but not physically, are ignored by the BusHead and no error message is generated.

This requires a configuration file, in which the commissioning engineer specifies the available equipment. When control is activated, this configuration is transferred in the form of a binary pattern to the BusHead, which analyzes it for comparison with the original configuration and applies the differences as the current status. If a module then fails during operation, this failure is identified according to the previous LioN-Link standard and signaled as a bus error. Only universal modules of type 0942 UEM 670 (8×M8) are used in the I/O area. The I/O memory area is always reserved for a complete assembly, irrespective of the respective equipment level.

The I/O modules can also be parameterized as dedicated input or output modules, whereby the I/O address space is not affected and is nevertheless reserved (shadow mode).






Effective Connectivity Solutions with LioN-Link Tool Changer Mode: 0940 PSL 603

The Fast System for Increasing Productivity and Efficiency

With the 0940 PSL 603 bus coupler module, Lumberg Automation™ has upgraded the LioN-Link product family for other areas of application and provides the options of quick and simple tool change.

The Lumberg Automation™ LioN-Link system can be connected or disconnected during operating time without affecting the superimposed Profibus strand. Bus errors are thus avoided. Areas of application in this case are tool couplings on automatic assembly machines or robot systems.

The LioN-Link system from Lumberg Automation™ saves both time and money and thus a permanent increase in productivity.





Effective Connectivity Solutions with LioN-Link Motion Drive Control: 0940 PSL 602 and 0942 UEM 620

Direct current drives are increasingly being utilized in many areas of automation technology for a wide variety of tasks. The advantages are obvious – small, compact, energy efficient drives with a high degree of performance efficiency. From a cost perspective, these drives often represent a good alternative to other solutions. However, integration into a uniform bus concept is often difficult. The components needed for this purpose are not readily available.

This gap has now been filled by a new module in the LioN-Link family from Lumberg Automation™ – Motion Drive Control. This system makes it possible to set up the connection between drives and the various bus systems.

The new module is equipped with four outlets that can be configured for brushless (EC) motors as well as for brush loaded (DC) motors and all types of digital actuators such as direct current motors or valves. Some of the special features of the LioN-Link Motion module include dynamic rpm control, parameterizable start/stop ramps for EC motors and an integrated brake resistance for DC motors.

These parameters can also be modified at any time during operation when a suitable control system is utilized. The demand for increased dynamics and maximum possible flexibility has been met as a result. The module also provides eight digital inputs. The wiring complexity is thus minimized for the sensor system allocated.

The good diagnostics capability that is a feature of the entire LioN-Link system is of course included with the Motion Drive Control distribution box. As a result, motor and sensor faults can be diagnosed according to channel, both visually and in the form of software messages. And of course we have also satisfied stringent requirements with respect to the type of protective system and resistance to vibrations and shocks, as is the case with the entire LioN-Link system.

Key Features

- Networking across multiple segments
- Each conveying zone is divided into segments. Multiple rollers are combined in each segment, i.e. communication with the bus system beyond this segment is possible
- · Utilization of standard sensors
- Reduced wiring complexity through the use of connectors
- Only one 24 V network, no AC network and no pneumatic components required
- Energy saving (savings potential can be realized with effective motor control, as the motors are only started when they are needed)
- Dynamic rpm control (acceleration and deceleration) allows soft startup and braking of the rollers
- Comprehensive diagnostics options
- Up to 10,000 motors with one fieldbus master
- LioN-Link: a compact system for I/O and motor control

Advantages for System Users

- Reduced operating costs, e.g. energy saving or control optimized utilization of rollers
- Minimal investment costs, good price/ performance ratio thanks to an optimum control concept
- Low maintenance costs thanks to standardized components. Rapid replacement through utilization of M8/M12 connectors

Advantages for Conveyor Manufacturers

- Activation via Profibus with diagnostic functionality and fault management
- Easy commissioning and installation thanks to minimal wiring complexity with M8/M12 connectors
- Variable motor roller running characteristics with acceleration and deceleration profiles, which can be optimized specifically for the product to be conveyed
- Interface to other fieldbus systems and Ethernet technologies

Advantages for System Integrators and Machine Builders

- · Very good diagnostics capability
- Low servicing costs loss thanks to durability and reliability
- LioN-Link: one system for all inputs and outputs plus motor control





Advantages of the LioN-Link System at a Glance

Per BusHead:

- 15 devices per line
- 100 m extension per line
- Unlimited distance between two devices up to maximum extension
- Cycle time approx. 2 ms
- No terminators
- Wiring with standard components:
 - Reduced variety of part types and costs
 - Easy purchasing worldwide (manufacturer independent)
- Input modules are supplied using the LioN-Link, no additional connection cable required
- Plug and play commissioning without special utilities
- Diagnostics for periphery faults and bus errors
- Visual differentiation of connections by means of color coding
- Low weight, ideal for small handling robots
- No module addressing and no terminator required
- Universal modules are configuration free
- Supply of safety critical actuators can take place decentrally in the field, no individual wiring
- Expansion of the PROFIBUS network WITHOUT repeaters and retaining the max. baud rate












0940 PSL 601



LioN-Link BusHead Profibus-Slave

LioN-Link BusHead IP 67 bus coupler module for the connection between the higher level fieldbus and the fieldbus independent I/O modules, with M12 bus connection, rotary switches for addressing, M12 LioN-Link connection, M12 power supply connection



Diagnostic Indication

LED	Indication	Condition
I/O Line 1, I/O Line 2	red green off	wrong configuration/module exchanged online, communication with PLC branch not in use (module not connected)
U _{S1}	green	sensor/system power supply Line 1
U _{S2}	green	sensor/system power supply Line 2
BF	red	bus error
DIA	red	common indication for periphery faults

Bus connection M12, B coded	LioN-Link connection M12	Power supply M12	
1 = +5 V 1 2 = Line A 3 = GND (0 V) 1 4 = Line B 5 = Earth	1 = Drain 2 = 24 V System 3 = 0 V System 4 = Data + 5 = Data -	$ \begin{array}{cccc} & & & & & & & & & & & \\ & & & & & & &$	

^{1 =} internal signals

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 200 g
Housing material PBT

Bus systemProfibus DPID number0A36 hexGSD fileLum_0A36.GSDTransmission ratemax. 12 MBaudAddress range1-125 decRotary address switches1-99 decDefault address99 dec

System/sensors

 $\begin{array}{lll} \textbf{power supply} & \textbf{U}_{S1}, \textbf{U}_{S2}^* \\ \textbf{Rated voltage} & 24 \text{ V DC} \\ \textbf{Voltage range} & 19 - 30 \text{ V DC} \\ \textbf{Power consumption} & \text{typ. 100 mA} \\ \textbf{Reverse polarity protection} & \text{yes} \\ \textbf{Indication} & \textbf{LED green} \\ \textbf{Output current per branch} & \text{max. 3 A} \\ \end{array}$

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Diagnosis according to Profibus specification, diagnosis for communication status, module breakdown and periphery faults in the Link system

Purpose

BusHead for LioN-Link standard modules

Designation

0940 PSL 601



^{*} Both supply points on the BusHead must always be connected.






0940 PSL 602



LioN-Link BusHead Profibus-Slave

LioN-Link BusHead IP 67 bus coupler module for the connection between the higher level fieldbus and the fieldbus independent I/O modules, with M12 bus connection, rotary switches for addressing, M12 LioN-Link connection, M12 power supply connection

Supports Profibus DP-V1 (acyclic communication)



Diagnostic Indication

LED	Indication	Condition
I/O Line 1, I/O Line 2	red green off	wrong configuration/module exchanged online, communication with PLC branch not in use (module not connected)
U _{S1}	green	sensor/system power supply Line 1
U _{S2}	green	sensor/system power supply Line 2
BF	red	bus error
DIA	red	common indication for periphery faults

Bus connection M12, B coded	LioN-Link connection M12	Power supply M12	
1 = +5 V 1 2 = Line A 3 = GND (0 V) 1 4 = Line B 5 = Earth	1 = Drain 2 = 24 V System 3 = 0 V System 4 = Data + 5 = Data -	$ \begin{array}{ccc} & 1 & = +24 \text{ V} \\ & 2 & = +24 \text{ V} \\ & 3 & = 0 \text{ V} \\ & 4 & = 0 \text{ V} \\ & 5 & = \text{Earth} \end{array} $	

^{1 =} internal signals

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 200 g
Housing material PBT

Bus systemProfibus DPID number0B99 hexGSD fileLum_0B99.GSDTransmission ratemax. 12 MBaudAddress range1-125 decRotary address switches1-99 decDefault address99 dec

System/sensors

 $\begin{array}{lll} \textbf{power supply} & \textbf{U}_{S1}, \textbf{U}_{S2}^* \\ \textbf{Rated voltage} & 24 \text{ V DC} \\ \textbf{Voltage range} & 19 - 30 \text{ V DC} \\ \textbf{Power consumption} & \textbf{typ. 100 mA} \\ \textbf{Reverse polarity protection} & \textbf{yes} \\ \textbf{Indication} & \textbf{LED green} \\ \textbf{Output current per branch} & \text{max. 3 A} \\ \end{array}$

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Diagnosis according to Profibus specification, diagnosis for communication status, module breakdown and periphery faults in the Link system

Purpose

BusHead for LioN-Link standard modules, Motion module "0942 UEM 783" and I/O-Link module "0942 UEM 620" $\,$

Designation

0940 PSL 602



^{*} Both supply points on the BusHead must always be connected.






0940 PSL 603



LioN-Link BusHead Profibus-Slave

LioN-Link BusHead IP 67 bus coupler module for the connection between the higher level fieldbus and the fieldbus independent I/O modules, with M12 bus connection, rotary switches for addressing, M12 LioN-Link connection, M12 power supply connection

 Profibus-Slave, for applications such as tool change or options handling with LioN-Link I/O module 0942 UEM 670



Diagnostic Indication

LED	Indication	Condition
I/O Line 1, I/O Line 2	red green off	wrong configuration/module exchanged online, communication with PLC branch not in use (module not connected)
U_{S1}	green	sensor/system power supply Line 1
Us2	green	sensor/system power supply Line 2
BF	red	bus error
DIA	red	common indication for periphery faults

Bus connection M12, B coded	LioN-Link connection M12	Power supply M12	
1 = +5 V 1 2 = Line A 3 = GND (0 V) 1 4 = Line B 5 = Earth	1 = Drain 2 = 24 V System 3 = 0 V System 4 = Data + 5 = Data -	$ \begin{array}{cccc} & & & & & & & & & & & \\ & & & & & & &$	

^{1 =} internal signals

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 200 g
Housing material PBT

Bus systemProfibus DPID number0B98 hexGSD fileLum_0B98.GSDTransmission ratemax. 12 MBaudAddress range1-125 decRotary address switches1-99 decDefault address99 dec

System/sensors

 $\begin{array}{lll} \textbf{power supply} & \textbf{U}_{S1}, \textbf{U}_{S2}^* \\ \textbf{Rated voltage} & 24 \text{ V DC} \\ \textbf{Voltage range} & 19 - 30 \text{ V DC} \\ \textbf{Power consumption} & \textbf{typ. 100 mA} \\ \textbf{Reverse polarity protection} & \textbf{yes} \\ \textbf{Indication} & \textbf{LED green} \\ \textbf{Output current per branch} & \text{max. 3 A} \\ \end{array}$

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Diagnosis according to Profibus specification, diagnosis for communication status, module breakdown and periphery faults in the Link system

Purpose

BusHead for LioN-Link standard modules, "shadow module 0942 UEM 670" and "tool change mode"

Designation

0940 PSL 603

UL T

^{*} Both supply points on the BusHead must always be connected.


CANopen

0940 CSL 601



LioN-Link BusHead CANopen®-Slave

LioN-Link BusHead IP 67 bus coupler module for the connection between the higher level fieldbus and the fieldbus independent I/O modules, with M12 bus connection, rotary switches for addressing, M12 LioN-Link connection, M12 power supply connection



Diagnostic Indication

LED	Indication	Condition
I/O Line 1, I/O Line 2	red green off	wrong configuration/module exchanged online, communication with PLC branch not in use (module not connected)
U _{S1}	green	sensor/system power supply Line 1
U_{S2}	green	sensor/system power supply Line 2
MS	green green flashing red red flashing red/green flashing	device is ready for operating wrong configuration unrecoverable fault recoverable fault self test is running
NS	green green flashing red flashing red	online, communication with PLC online, no communication with PLC timeout state of one or more I/O connections failed communication device, BUS-OFF status, duplicate MAC-ID

Bus connection M12	LioN-Link connection M12	Power supply M12	
1 = Drain 2 = 24 V 3 = GND (0 V) 4 = CAN_H 5 = CAN_L Housing / = Earth	1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	$ \begin{array}{cccc} & & & & & & 1 & = +24 \text{ V} \\ & & & & & 2 & = +24 \text{ V} \\ & & & & 2 & = +24 \text{ V} \\ & & & & 3 & = 0 \text{ V} \\ & & & & 4 & = 0 \text{ V} \\ & & & 5 & = \text{Earth} \end{array} $	

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 200 g
Housing material PBT

Bus systemCANopen®GSD/EDS file0940CSL601.EDSTransmission ratemax. 1 MBaudAddress range1–99 decRotary address switches1–99 decDefault address63 dec

Supply of the

fieldbus interfaceUsRated voltage24 V DCVoltage range11-30 V DCPower consumptiontyp. 10 mAReverse polarity protectionyesIndicationLED green

System/sensors

 $\begin{array}{lll} \textbf{power supply} & \textbf{U}_{S1}, \textbf{U}_{S2}^{*} \\ \textbf{Rated voltage} & 24 \, \text{V DC} \\ \textbf{Voltage range} & 19-30 \, \text{V DC} \\ \textbf{Power consumption} & \textbf{system: typ. 60 mA/} \end{array}$

system: typ. 60 mA / fieldbus: typ. 10 mA

Reverse polarity protection yes
Indication LED green
Output current per branch max. 3 A

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Diagnosis for communication status, module breakdown and periphery faults in the Link system

Note

A maximum of 16 LioN-Link I/O modules can be operated on this BusHead

Designation

0940 CSL 601



^{*} Both supply points on the BusHead must always be connected.

A BELDEN BRAND




0940 DSL 601



LioN-Link BusHead DeviceNet-Slave

LioN-Link BusHead IP 67 bus coupler module for the connection between the higher level fieldbus and the fieldbus independent I/O modules, with M12 bus connection, rotary switches for addressing, M12 LioN-Link connection, M12 power supply connection



Bit Assignment

Bit	7	6	5	4	3	2	1	0
				Inpu	t			
Byte 0	0	0	0	0	US1	US2	KS1	KS2
Byte 1	DIAG							
	S_8	S_7	S_6	S_5	S_4	S_3	S_2	S_1
Byte 2	DIAG							
	S_16	S_15	S_14	S_13	S_12	S_11	S_10	S_9
Byte 3	STATUS							
	S_8	S_7	S_6	S_5	S_4	S_3	S_2	S_1
Byte 4	STATUS							
	S_16	S_15	S_14	S_13	S_12	S_11	S_10	S_9

USx: Low voltage Line x KSx: Short circuit on Line x DIAG S_x: Diagnostic message I/O module x STATUS S_x: Configuration error I/O module x

Diagnostic Indication

LED	Indication	Condition
I/O Line 1, I/O Line 2	red green off	wrong configuration/module exchanged online, communication with PLC branch not in use (module not connected)
Us	green	power supply of fieldbus interface
U_{S1}	green	sensor/system power supply Line 1
U _{S2}	green	sensor/system power supply Line 2
MS	green green flashing red red flashing red/green flashing	device is ready for operating wrong configuration unrecoverable fault recoverable fault self test is running
NS	green green flashing red flashing red	online, communication with PLC online, no communication with PLC timeout state of one or more I/O connections failed communication device, BUS-OFF status, duplicate MAC-ID

Bus connection M12	LioN-Link connection M12	Power supply M12	
1 = Drain 2 = 24 V 3 = GND (0 V) 3	1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	$ \begin{array}{ccc} \stackrel{4}{\bullet} & \stackrel{\bullet}{\bullet} & \stackrel{3}{\bullet} & 1 = +24 \text{ V} \\ \stackrel{\bullet}{\bullet} & \stackrel{\bullet}{\bullet} & 2 = +24 \text{ V} \\ & & & & & & \\ & & & & & & \\ & & & & &$	

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 200 g
Housing material PBT

Bus system DeviceNet

EDS file 00_0940DSL601.eds
Transmission rate max. 500 kBaud
Address range 1-63 dec
Rotary address switches 1-63 dec
Default address 63 dec

Supply of the

fieldbus interfaceUsRated voltage24 V DCVoltage range11-30 V DCPower consumptiontyp. 10 mAReverse polarity protectionyesIndicationLED green

System/sensors

 $\begin{array}{lll} \textbf{power supply} & \textbf{U}_{S1}, \textbf{U}_{S2}^* \\ \textbf{Rated voltage} & 24 \, \text{V DC} \\ \textbf{Voltage range} & 19 - 30 \, \text{V DC} \\ \textbf{Power consumption} & \textbf{typ. 50 mA} \\ \textbf{Reverse polarity protection} & \textbf{yes} \\ \textbf{Indication} & \textbf{LED green} \\ \textbf{Output current per branch} & \text{max. 3 A} \\ \end{array}$

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Diagnosis for communication status, module breakdown and periphery faults in the Link system

Note

A maximum of 16 LioN-Link I/O modules can be operated on this BusHead

Designation

0940 DSL 601



^{*} Both supply points on the BusHead must always be connected.






0940 ESL 601




LioN-Link BusHead ProfiNet-I/O-Device-Slave (ProfiNet LAN)

LioN-Link BusHead IP 67 bus coupler module for the connection between the higher level fieldbus and the fieldbus independent I/O modules, with M12 LioN-Link connection, M12 power supply connection

 M12 LAN connection, D coded, integrated
 3-port switch, web server, IRT (Isochrone Real Time communication)





Diagnostic Indication

LED	Indication	Condition
I/0 _{S1}	red green	wrong configuration/module exchanged online, communication with PLC
1/0s2	red green off	wrong configuration/module exchanged online, communication with PLC branch not in use
U_{S1}	green	sensor/system power supply Line 1
U _{S2}	green	sensor/system power supply Line 2
LNK/ACT	green orange (flashing)	connection to an Ethernet device I/O device exchanging data
BF	red	no I/O controller or wrong LioN-Link configuration
DIA	red	common indication for periphery faults

LAN connection M12, D coded	LioN-Link connection M12	Power supply M12
1 = TD+ 2 = RD+ 3 = TD- 4 = RD- Housing = Shield	1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	$ \begin{array}{ccccc} & & & & & & \\ & & & & & \\ & & & & & $

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 800 g
Housing material PBT

Bus systemPROFINET IOVendorID0016A hexDeviceID0302 hex

GSDML file gsdml-v2.2-Lumberg Automation-LioN Link-20090623.xml

Transmission rate 100 Mbit/s full duplex

Transmission method 100Base-TX

Default IP address 0

System/sensors

 $\begin{array}{lll} \textbf{power supply} & \textbf{U}_{S1}, \textbf{U}_{S2}^* \\ \textbf{Rated voltage} & 24 \text{ V DC} \\ \textbf{Voltage range} & 19 - 30 \text{ V DC} \\ \textbf{Power consumption} & \textbf{typ. 100 mA} \\ \textbf{Reverse polarity protection} & \textbf{yes} \\ \textbf{Indication} & \textbf{LED green} \\ \textbf{Output current per branch} & \text{max. 3 A} \\ \end{array}$

Connection M12 plug insert (5 poles), see pin assignment

Included in

delivery/accessories Dust covers M12, attachable labels

Purpose

BusHead for LioN-Link standard modules, Motion module "0942 UEM 783" and I/O-Link module "0942 UEM 620" $\,$

Designation

0940 ESL 601




^{*} Both supply points on the BusHead must always be connected.

LioN-Link I/O Module with 8 Digital Inputs and Outputs

0942 UEM 650



8 IN/8 OUT universalLioN-Link I/O module with 8 digital I/O channels, channels can be used universally as inputs or outputs, M8 sockets (8x), 3 poles, M12 actuator supply



Bit Assignment

Bit	7	6	5	4	3	2	1	0
			M	3 Input	t			
Byte 0	8	7	6	5	4	3	2	1
M8 Output								
Byte 0	8	7	6	5	4	3	2	1

Diagnostic Indication

LED	Indication	Condition
18	yellow	channel status
18	red	periphery faults (actuator short circuit/overload)
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	actuator power supply
DIA	red	common indication for periphery faults

LioN-Link connection M12	Actuator/sensor connection M8	Actuator supply M12
1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	$ \begin{array}{ccc} 4 & & & & \\ & & & & \\ & & & & \\ & & & & \\ & & & & $

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 175 g
Housing material PBT

System/sensors

power supplyUsRated voltage24 V DCVoltage range19 – 30 V DCPower consumptiontyp. 70 mAOperating indicationLED green

Input power supply U_S

Voltage range min. (Usystem – 1.5 V) Sensor current 700 mA/module

Short circuit proof yes
Indication LED green

Input wiring Type 3 acc. to IEC 61131-2

Rated input voltage 24 V DC
Channel type N.O. p-switching
Number of digital channels max. 8

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

 $\begin{array}{ll} \mbox{Output power supply} & \mbox{U_L} \\ \mbox{Rated voltage} & 24 \mbox{ V DC} \\ \mbox{Voltage range} & 19 - 30 \mbox{ V DC} \end{array}$

Reverse polarity protection yes/antiparallel diode

Indication LED green

Output wiring

Rated output current 0.5 A per channel

Short circuit proof yes

Max. output current 4 A per module

Overload proof yes
Number of digital channels max. 8
Channel type N.O. p-switching

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

Included in

delivery/accessories Dust covers M12,

attachable labels

Diagnostic

Periphery fault diagnosis for sensor short circuit, actuator short circuit, sensor low voltage detection

Designation

0942 UEM 650




LioN-Link I/O Module with 8 Digital Inputs

0942 UEM 651



8 IN

LioN-Link I/O module with 8 digital inputs to connect standard sensors, M8 sockets (8x), 3 poles



Bit Assignment

Bit	7	6	5	4	3	2	1	0
M8 Input								
Byte 0	8	7	6	5	4	3	2	1

Diagnostic Indication

LED	Indication	Condition
18	yellow	channel status
18	red	periphery fault
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
DIA	red	common indication for periphery faults

Pin Assignment

LioN-Link connection M12

Actuator/sensor connection M8

1 = Drain
2 = 24 V Sensor/System
3 = 0 V Sensor/System
4 = Data +
5 = Data -

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 175 g
Housing material PBT

System/sensors

power supplyUsRated voltage24 V DCVoltage range19 – 30 V DCPower consumptiontyp. 70 mAOperating indicationLED green

Input power supply U_S

Voltage range min. (U_{System} – 1.5 V) Sensor current 700 mA/module

Short circuit proof yes Indication LED green

Input wiring Type 3 acc. to IEC 61131-2

Rated input voltage 24 V DC
Channel type N.O. p-switching
Number of digital channels max. 8

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Periphery fault diagnosis for sensor short circuit, sensor low voltage detection

Designation

0942 UEM 651




LioN-Link I/O Module with 8 Digital Inputs and Outputs

0942 UEM 600



8 IN/8 OUT

universal LioN-Link I/O module with 8 digital I/O channels, channels can be used universally as inputs or outputs, M12 sockets (4x), 5 poles, M12 actuator supply



Bit Assignment

Bit	7	6	5	4	3	2	1	0
M12 Input								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A
M12 Output								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A

Diagnostic Indication

LED	Indication	Condition
14 A/B	yellow	channel status
14 A/B	red	periphery fault
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	actuator power supply
DIA	red	common indication for periphery faults

N-Link connection M12	Actuator/sensor connection M12	Actuator supply M12
1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	$ \begin{array}{c} 4 \\ \bullet \bullet \bullet \\ 1 \\ \bullet \bullet \bullet \\ 5 \end{array} $ $ \begin{array}{c} 1 = +24 \text{ V} \\ 2 = \text{ n.c.} \\ 3 = \text{ GND (0 V)} \\ 4 = \text{ n.c.} \\ 5 = \text{ Earth} $

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 200 g
Housing material PBT

System/sensors

power supply

Rated voltage

Voltage range

Power consumption

Operating indication

Us

24 V DC

19 – 30 V DC

typ. 70 mA

LED green

Input power supply U_S

Voltage range min. (U_{System} – 1.5 V) Sensor current 700 mA/module

Short circuit proof yes
Indication LED green

Input wiring Type 3 acc. to IEC 61131-2

Rated input voltage 24 V DC
Channel type N.O. p-switching
Number of digital channels max. 8

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

 $\begin{array}{ll} \mbox{Output power supply} & \mbox{U}_L \\ \mbox{Rated voltage} & 24 \mbox{ V DC} \\ \mbox{Voltage range} & 19 - 30 \mbox{ V DC} \end{array}$

Reverse polarity protection yes/antiparallel diode

Indication LED green

Output wiring

Rated output current 1.6 A per channel

Short circuit proof yes

Max. output current 4 A per module

Overload proof yes
Number of digital channels max. 8
Channel type N.O. p-switching

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

Included in delivery/accessories

Dust covers M12, attachable labels

Diagnostic

Periphery fault diagnosis for sensor short circuit, actuator short circuit/channel, sensor low voltage detection

Designation

0942 UEM 600




LioN-Link I/O Module with 8 Digital Inputs

0942 UEM 601



8 IN

LioN-Link I/O module with 8 digital inputs to connect standard sensors, M12 sockets (4x), 5 poles




Bit Assignment

Bit	7	6	5	4	3	2	1	0
M12 Input								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A

Diagnostic Indication

LED	Indication	Condition
14 A/B	yellow	channel status
14 A	red	periphery fault
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
DIA	red	common indication for periphery faults



Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 175 g
Housing material PBT

System/sensors

power supplyUsRated voltage24 V DCVoltage range19 – 30 V DCPower consumptiontyp. 70 mAOperating indicationLED green

Input power supply U_S

Voltage range min. (U_{System} – 1.5 V) Sensor current 700 mA/module

Short circuit proof yes
Indication LED green

Input wiring Type 3 acc. to IEC 61131-2

Rated input voltage 24 V DC
Channel type N.O. p-switching
Number of digital channels max. 8

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Periphery fault diagnosis for sensor short circuit, sensor low voltage detection

Designation

0942 UEM 601




LioN-Link I/O Module with 4 Analog Inputs

0942 UEM 630



4 IN

LioN-Link I/O module with 4 analog inputs 0(4) - 20 mA to connect standard sensors, M12 sockets (4x), 5 poles




Bit Assignment

Bit	7	6	5	4	3	2	1	0
				M12 I	nput			
Byte 0 Byte 1	Channel 1							
Byte 2 Byte 3	Channel 2							
Byte 4 Byte 5	Channel 3							
Byte 6 Byte 7	Channel 4							

Diagnostic Indication

LED	Indication	Condition
14	yellow	channel status
14 DIA	red	periphery fault
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
DIA	red	common indication for periphery faults



Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 175 g
Housing material PBT

Input power supplyUsVoltage range24 V DCSensor current700 mA/module

Short circuit proof yes

Power consumption system: typ. 50 mA

Input wiringCurrent inputsMeasurement signal(0)4–20 mAResolution12 bit + signMeasuring fault (full measuring range) $\pm 1.2\%$ Temperature fault (full measuring range) $\pm 0.01\%/K$ Output formatsSiemens S7Input impedance $≤ 400 \Omega$

Conversion time typ. 25 ms per channel

Potential separation

channel/channel no

Potential separation

power/channel no Number of analog channels max. 4

Channel status indicator LED yellow: channel active

Module diagnostic Module status Sensor short circuit

Indication LED red/green (I/O)

Channel diagnostic

0-20 mA Overload at current measurement

4-20 mA Overload at current measurement/Underflow/Broken wire

Indication LED red (DIA)

GSD configuration

Module way Resolution 12 bit, 10 bit (Conversion time ≤3 ms/module)

Channel way Measuring range 0 – 20 mA or 4 – 20 mA

Broken wire (only 4–20 mA), Channel on/off, Diagnostic on/off

Included in

delivery/accessories Dust covers M12, attachable labels

Designation

0942 UEM 630




LioN-Link I/O Module with 4 Analog Inputs

0942 UEM 631



4 IN

LioN-Link I/O module with 4 analog inputs 0–10 V to connect standard sensors, M12 sockets (4x), 5 poles




Bit Assignment

Bit	7	6	5	4	3	2	1	0
				M12 lı	nput			
Byte 0 Byte 1				Chanr	nel 1			
Byte 2 Byte 3	Channel 2							
Byte 4 Byte 5	Channel 3							
Byte 6 Byte 7	Channel 4							

Diagnostic Indication

LED	Indication	Condition
14	yellow	channel status
14 DIA	red	periphery fault
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
DIA	red	common indication for periphery faults



Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 175 g
Housing material PBT

 $\begin{array}{ll} \text{Input power supply} & \text{U}_S \\ \text{Voltage range} & 24 \text{ V DC} \\ \text{Sensor current} & 700 \text{ mA/module} \end{array}$

Short circuit proof yes

Power consumption system: typ. 50 mA

 Input wiring
 Voltage inputs

 Measurement signal
 0-10 V

 Resolution
 12 bit + sign

 Measuring fault (full measuring range)
 ±1.2 %

 Temperature fault (full measuring range)
 ±0.01 %/K

 Output formats
 Signess \$7

Output formats Siemens S7 Input impedance 20 $k\Omega$

Conversion time typ. 25 ms per channel

Potential separation

channel/channel no

Potential separation

power/channel no Number of analog channels max. 4

Channel status indicator LED yellow: channel active

Module diagnostic Module status Sensor short circuit

Indication LED red/green (I/O)

Channel diagnosticOverflowIndicationLED red (DIA)

GSD configuration

Module way Resolution 12 bit, 10 bit (Conversion time ≤3 ms/module)

Channel way Channel on/off, Diagnostic on/off

Included in

delivery/accessories Dust covers M12, attachable labels

Designation

0942 UEM 631




LioN-Link I/O Module with 8 Digital Inputs and 4 Digital or Analog Outputs (Motion Drive Control)



8 IN/4 OUT (digital or analog)

LioN-Link Motion module with 8 digital inputs and 4 universal outputs that can be configured for the connection of brushless motors, DC motors or for valves. System specific specifications such as speed and acceleration/deceleration can be transmitted via the DP-V1* protocol. Power supply is via a connecting cable with 7/8" connector.

* = Only with 0940 PSL 602



Bit Assignment

Bit	7	6	5	4	3	2	1	0
			M	12 Inpu	ıt			
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A
			M1	2 Outp	ut			
	Soc	ket 8	Soci	ket 7	Soci	cet 6	Soc	ket 5
Byte 0	Dir	Start	Dir	Start	Dir	Start	Dir	Start

Diagnostic Indication

LED	Indication	Condition
14 A/B	yellow	channel status
14 A/B	red	periphery faults (actuator short circuit/overload)
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	actuator power supply
DIA	red	common indication for periphery faults

LioN-Link connection M12	Actuator/sensor connection M12			Power supply for motors			
$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	3 0 0 4 0 0 1	In 1 = +24 V DC 2 = In B 3 = 0 V 4 = In A 5 = Earth	Out 1 = +24 V DC 2 = Dir 3 = 0 V 4 = Dia 5 = Speed (0-10 V)	3 ()	Function 1 = Diag. Out 2 = +24 V 3 = 0 V	Wire colo Black Brown Blue	

IP 67 Degree of protection -10°C/+60°C Operating temperature range Weight 175 g Housing material PBT

System/sensors

power supply Us Rated voltage 24 V DC 19-30 V DC Voltage range Power consumption typ. 100 mA Reverse polarity protection Operating indication LED green

Input power supply Us 24 V DC Voltage range Sensor current 700 mA/module

Short circuit proof ves Indication LED green

M12 connector (5 poles), Connection see pin assignment

Input wiring Type 3 acc. to IEC 61131-2

24 V DC

yes

typ. 5 mA

LED red per channel

see pin assignment

M12 coupling (5 poles),

Rated input voltage Input current at 24 V DC

Short circuit proof sensor supply

Channel type N.O. p-switching Number of digital channels max. 8 Channel status indicator LED yellow per channel

Diagnostic indication Connection

Output power supply 24 V DC Rated voltage 19-27 V DC Voltage range

Reverse polarity protection yes/antiparallel diode

Indication LED green

7/8" connector (3 poles), see pin Connection

assignment

Output wiring I

Rated output current

Signal status "1" Signal status "0" Short circuit proof Max. output current Overload proof Number of digital channels Channel type N.O. Channel status indicator Diagnostic indication Connection

Output wiring II

Voltage range Number of channels Channel type Connection

Included in delivery/accessories see pin assignment Output module Pin 5

LED yellow per channel

M12 coupling (5 poles),

LED red per channel

0-10 V DC (motor dependent) max. 4 analog PWM output M12 coupling (5 poles), see pin assignment

Type 3 acc. to IEC 61131-2 Output module Pin 2

max. 1 mA (standard specification)

1.5 A per channel

7.2 A per module

yes

ves

max. 4

p-switching

max. 4 A (max. 50 ms)

Dust covers M12, attachable labels

Diagnostic

Periphery fault diagnosis for sensor short circuit, actuator short circuit/channel, sensor low voltage detection

Note

Only to be used in combination with BusHead 0940 PSL 602. Module used to control brushless (EC) motors as well as brush loaded (DC) motors and all types of digital actuators (e.g. valves or direct current motors)

Designation

0942 UEM 783









LioN-Link I/O Module with 8 Digital Inputs and Outputs (Shadow Mode)

0942 UEM 670





8 IN/8 OUT universal

LioN-Link I/O module with 8 digital I/O channels, channels can be used universally as inputs or outputs, M8 sockets, 3 poles

Input or output functionality can be switched off while retaining the respective address range*.

* = Only with 0940 PSL 603





Bit Assignment

Bit	7	6	5	4	3	2	1	0
			M	3 Input	t			
Byte 0	8	7	6	5	4	3	2	1
			M8	Outpu	ıt			
Byte 0	8	7	6	5	4	3	2	1

Diagnostic Indication

LED	Indication	Condition
18	yellow	channel status
18	red	periphery faults (actuator short circuit/overload)
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	actuator power supply
DIA	red	common indication for periphery faults

LioN-Link connection M12	Actuator/sensor connection M8	Actuator supply M12
1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	$ \begin{array}{cccc} & & & & & & \\ & & & & & \\ & & & & & $

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 175 g
Housing material PBT

System/sensors

power supplyUsRated voltage24 V DCVoltage range19 – 30 V DCPower consumptiontyp. 70 mAOperating indicationLED green

 $\begin{array}{lll} \text{Input power supply} & \text{U}_S \\ \text{Voltage range} & 24 \text{ V DC} \\ \text{Sensor current} & 700 \text{ mA/module} \end{array}$

Short circuit proof yes
Indication LED green

Input wiring Type 3 acc. to IEC 61131-2

Rated input voltage 24 V DC
Channel type N.O. p-switching
Number of digital channels max. 8

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

 $\begin{array}{ll} \mbox{Output power supply} & \mbox{U_L} \\ \mbox{Rated voltage} & 24 \mbox{ V DC} \\ \mbox{Voltage range} & 19 - 30 \mbox{ V DC} \\ \end{array}$

Reverse polarity protection yes/antiparallel diode

Indication LED green

Output wiring

Rated output current 0.5 A per channel

Short circuit proof yes

Max. output current 4 A per module

Overload proof yes
Number of digital channels max. 8
Channel type N.O. p-switching

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

Included in

delivery/accessoriesDust covers M12, attachable labels

Diagnostic

Periphery fault diagnosis for sensor short circuit, actuator short circuit, sensor low voltage detection

Note

This I/O module can only be used with the BusHead 0940 PSL 603.

In addition to being used as a dedicated input or output module, this module can also be operated in Shadow Input and Shadow Output mode.

The process data in both modes is 1 input and 1 output byte. In Shadow Input mode the input byte is set to 0. The outputs can be activated via the output byte. In Shadow Output mode, however, the outputs cannot be activated and the inputs can be used normally.

Designation

0942 UEM 670



OIO-Link

0942 UEM 620




LioN-Link I/O Module with 8 Digital Inputs and 4 I/O-Link Inputs (I/O-Link-Master)

8 IN/4 I/O-Link IN universal

LioN-Link I/O module with 4 I/O-Link channels, each channel can be configured universally in standard digital I/O mode (SIO mode) or in communications mode, M12 sockets, 4 poles

 Only with BusHead 0940 PSL 602 or ProfiNet BusHead 0940 ESL 601



Diagnostic Indication

LED	Indication	Condition
14 A IOL:	green	I/O-Link communications mode
14 B DIA:	yellow red flashing red	standard I/O mode (SIO) I/O-Link diagnostic: IOL fault SIO mode: periphery fault
1/0	yellow red red flashing green	channel status in SIO mode wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	I/O-Link supply
DIA	red	common indication for periphery faults

LioN-Link connection M12	I/O-Link connection M12	I/O-Link supply M12
1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	1 = +24 V DC 2 = In B 3 = (0 V) 4 = IO-Data/In A 5 = Earth	$ \begin{array}{c} $

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 175 g
Housing material PBT

System/sensors

power supplyUsRated voltage24 V DCVoltage range19 – 30 V DCPower consumptiontyp. 70 mAOperating indicationLED green

Input power supplyUsVoltage range24 V DC

Sensor current 700 mA/module

Short circuit proof yes Indication LED green

Input wiring Type 3 acc. to IEC 61131-2

Rated input voltage 24 V DC
Channel type N.O. p-switching
Number of digital channels max. 8

Channel status indicator LED A green/yellow

Diagnostic indication LED red

 $\begin{tabular}{ll} I/O-Link power supply & U_L \\ Rated voltage & 24 V DC$ \\ Voltage range & 19-30 V DC \\ \end{tabular}$

Reverse polarity protection yes/antiparallel diode

Indication

I/O-Link Specification 1.0

Included in

delivery/accessories Dust covers M12, attachable labels

LED green

Note

The information in the operating instructions must be observed

Bit Assignment

					Ch	annel 1:	1 byte,	1 word	or not co	nfigure	i					
Byte				Byte 0)								Byte 1			
Bit	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Port				1									1			
					Ch	annel 2:	1 byte,	1 word	or not co	nfigure	i					
Byte				Byte 2	2								Byte 3			
Bit	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Port				2									2			
Assignment	1/0	-Link-	Device	process	data/Hig	jh Byte				1/0	-Link-D	evice pı	rocess o	ata/Lo	w Byte	
					Ch	annel 3:	1 byte,	1 word	or not co	nfigure	i					
Byte				Byte 4	ļ								Byte 5			
Bit	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Port				3									3			
Assignment	1/0	-Link-	Device	process	data/Hig	jh Byte				1/0	-Link-D	evice pı	ocess o	ata/Lo	w Byte	
					Ch	annel 4:	1 byte,	1 word	or not co	nfigure	i					
Byte				Byte 6	i								Byte 7			
Bit	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Port				4									4			
Assignment	1/0	-Link-	Device	process	data/Hig	jh Byte				1/0	-Link-D	evice pı	rocess o	ata/Lo	w Byte	
						2	Bytes (module	status)							
Byte				Byte 8	3								Byte 9			
Bit	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Port					4	3	2	1	4	3	2	1	4	3	2	1
Assignment					Pin 4 = DI	1=I0-Link 0=SI0	1=I0-Link 0=SI0	1=I0-Link 0=SI0	1=I0-Link 0=SI0	Pin 2 = DI						

Designation

0942 UEM 620




LioN-Link I/O Module with 16 Digital Inputs and Outputs

0942 UEM 700



16 IN/16 OUT universal

LioN-Link I/O module with 16 digital I/O channels, channels can be used universally as inputs or outputs, M12 sockets (8x), 5 poles, 7/8" actuator supply



Bit Assignment

Bit	7	6	5	4	3	2	1	0
			M1	2 Inpu	t			
Byte 0 Byte 1	4B 8B	4A 8A	3B 7B	3A 7A	2B 6B	2A 6A	1B 5B	1A 5A
			M12	Outp	ut			
Byte 0 Byte 1	4B 8B	4A 8A	3B 7B	3A 7A	2B 6B	2A 6A	1B 5B	1A 5A

Diagnostic Indication

LED	Indication	Condition
18 A/B	yellow	channel status
18	red	periphery faults (actuator short circuit/overload)
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	actuator power supply
DIA	red	common indication for periphery faults

LioN-Link connection M12	Actuator/sensor connection M12	Actuator supply 7/8"
1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	1 = +24 V 2 = In/Out B 3 = 0 V 4 = In/Out A 5 = Earth	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$

IP 67 Degree of protection Operating temperature range -10°C/+60°C Weight 375 g Housing material PBT

System/sensors

 U_{S} power supply 24 V DC Rated voltage 19-30 V DC Voltage range Power consumption typ. 100 mA

Input power supply U_{S}

Voltage range min. (U_{System} - 1.5 V)

700 mA Sensor current Short circuit proof yes Indication LED green

Type 3 acc. to IEC 61131-2 Input wiring

Rated input voltage 24 V DC Channel type N.O. p-switching Number of digital channels max. 16

Channel status indicator LED yellow per channel

Output power supply 24 V DC Rated voltage Voltage range 19-30 V DC

Reverse polarity protection yes/antiparallel diode

Indication LED green

Output wiring

Rated output current 1.6 A per channel

Short circuit proof

Max. output current 9 A (12 A*) per module

*Test proven and approved under the following conditions:
-Looped through sensor/system power supply max. 2.5 A
-Power supply cable STL 204 (5 x 1.00 mm²)

· Operating temperature range max. 40°C Overload proof

Number of digital channels max. 16 Channel type N.O. p-switching

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

Designation

0942 UEM 700



The application of these products in harsh environments should always be checked before use. Specifications subject to alteration.

Diagnostic

Periphery fault diagnosis for sensor short circuit, actuator short circuit, sensor low voltage detection


LioN-Link I/O Module with 16 Digital Inputs

0942 UEM 701



16 IN

LioN-Link I/O module with 16 digital inputs to connect standard sensors, M12 sockets (8x), 5 poles




Bit Assignment

Bit	7	6	5	4	3	2	1	0
M12 Input								
Byte 0	4B	4A	3B	3A	2B	2A	1B	1A
Byte 1	8B	8A	7B	7A	6B	6A	5B	5A

Diagnostic Indication

LED	Indication	Condition
18 A/B	yellow	channel status
18 A	red	periphery faults (actuator short circuit/overload)
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
DIA	red	common indication for periphery faults



Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 275 g
Housing material PBT

System/sensors

 $\begin{array}{ll} \textbf{power supply} & \textbf{U}_{\textbf{S}} \\ \textbf{Rated voltage} & 24 \text{ V DC} \\ \textbf{Voltage range} & 19-30 \text{ V DC} \\ \textbf{Power consumption} & \textbf{typ. 100 mA} \\ \end{array}$

Input power supply Us

Voltage range min. (U_{System} – 1.5 V)

Sensor current 700 mA
Short circuit proof yes
Indication LED green

Input wiring Type 3 acc. to IEC 61131-2

Rated input voltage 24 V DC
Channel type N.O. p-switching
Number of digital channels max. 16

Channel status indicator LED yellow per channel

Diagnostic

Periphery fault diagnosis for sensor short circuit, sensor low voltage detection

Designation

0942 UEM 701




LioN-Link I/O Module with 4 Digital Outputs

0942 UEM 602



4 OUT

LioN-Link I/O module with 4 digital outputs, M12 sockets (4x), 5 poles, 2 A per channel, one channel per socket



Bit Assignment

Bit	7	6	5	4	3	2	1	0
M12 Output								
Byte 0	-	_	_	_	4A	3 A	2A	1A

Diagnostic Indication

LED	Indication	Condition
14 A	yellow	channel status
14 DIA	red	periphery fault/output active with no actuator supply voltage
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	actuator power supply
DIA	red	common indication for periphery faults

LioN-Link connection M12	Actuator connection M12	Actuator supply M12
1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	$ \begin{array}{ccc} 4 & \bullet & \bullet & \bullet \\ 1 & \bullet & \bullet & \bullet \\ 1 & \bullet & \bullet & \bullet & \bullet \\ 2 & = +24 \text{ V DC} \\ 3 & = \text{ GND 0 V} \\ 4 & = \text{ GND 0 V} \\ 5 & = \text{ Functional earth} \end{array} $

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 200 g
Housing material PBT

System/sensors

 $\begin{array}{ll} \textbf{power supply} & \textbf{U}_{S} \\ \textbf{Rated voltage} & 24 \text{ V DC} \\ \textbf{Voltage range} & 19-30 \text{ V DC} \\ \textbf{Power consumption} & \textbf{typ. 70 mA} \\ \end{array}$

 $\begin{array}{ll} \textbf{Output power supply} & \textbf{U}_L \\ \text{Rated voltage} & 24 \, \text{V DC} \\ \text{Voltage range} & 19 - 30 \, \text{V DC} \end{array}$

Reverse polarity protection yes/antiparallel diode

Indication LED green

Connection M12 connector (3 or 5 poles)

Output wiring

Rated output current 2.0 A per channel

Short circuit proof yes

Max. output current 4 A (3 pole supply line); 6 A (5 pole supply line)

Overload proof yes
Number of digital channels max. 4
Channel type N.O. p-switching

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Periphery fault diagnosis for actuator short circuit/overload per channel

Note

Particularly suitable for the control of hydraulic valves

Designation

0942 UEM 602



LioN-Link I/O Module with 4 Digital Outputs


0942 UEM 612



4 OUT

LioN-Link I/O module with 4 digital outputs, M12 sockets (4x), 5 poles, M12 actuator supply, 2 A per channel, one channel per socket

- Suitable for safety critical applications within Performance Levels A through D



Bit Assignment

Bit	7	6	5	4	3	2	1	0	
M12 Output									
Byte 0	_	_	_	_	4 A	3 A	2A	1A	

Diagnostic Indication

LED	Indication	Condition
14 A	yellow	channel status
14 DIA	red	periphery fault/output active with no actuator supply voltage
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	actuator power supply
DIA	red	common indication for periphery faults

LioN-Link connection M12	Actuator connection M12	Actuator supply M12
1 = Drain 2 = 24 V Sensor/System 3 = 0 V Sensor/System 4 = Data + 5 = Data -	$ \begin{array}{cccccccccccccccccccccccccccccccccccc$	$ \begin{array}{c} $

Degree of protection IP 67
Operating temperature range -10°C/+60°C
Weight 200 g
Housing material PBT

System/sensors

 $\begin{array}{lll} \textbf{power supply} & \textbf{U}_S \\ \textbf{Rated voltage} & 24 \text{ V DC} \\ \textbf{Voltage range} & 19-30 \text{ V DC} \\ \textbf{Power consumption} & \textbf{typ. 70 mA} \\ \textbf{Operating indication} & \textbf{LED green} \\ \end{array}$

 $\begin{array}{ll} \text{Output power supply} & \quad \textbf{U}_L \\ \text{Rated voltage} & \quad 24 \, \text{V DC} \end{array}$

Voltage range 19 – 28.8 V DC (SELV/PELV acc. to EN60950-1) Reverse polarity protection yes/antiparallel diode, external fuse with

4/6 A medium time lag mandatory

Indication LED green

Connection M12 connector (3 or 5 poles)

Output wiring

Rated output current 2.0 A per channel

Short circuit proof yes

Max. output current 4 A (3 pole supply line); 6 A (5 pole supply line)

Overload proof yes
Number of digital channels max. 4
Channel type N.O. p-switching

Channel status indicator LED yellow per channel Diagnostic indication LED red per channel

Included in

delivery/accessories Dust covers M12, attachable labels

Diagnostic

Periphery fault diagnosis for actuator short circuit/overload per channel

Designation

0942 UEM 612



The application of these products in harsh environments should always be checked before use. Specifications subject to alteration.

Note

Due to the need to guarantee reliable, all pole disconnection of the output voltage supply on the customer side, utilization in emergency power off circuits is possible for applications up to Performance Level D. The absence of reaction between the logic and output supply circuits in the event of a hardware fault in the module is guaranteed.


The instructions in the LioN-Link manual must be observed in this case.

LioN-Link I/O Module with 16 Digital Inputs and Outputs

0942 UEM 780

16 IN/16 OUT universal

LioN-Link I/O module with 16 digital I/O channels, channels can be used universally as inputs or outputs, multipole cable interface to connect valve terminals, control consoles, manual tool changing devices, IP20 terminal boxes




Bit Assignment

Bit	7	6	5	4	3	2	1	0
			M	l12 Inp	ut			
Byte 0 Byte 1	RD YE/BN	BU WH/YE	PK BN/GN	GY WH/GN	YE RD/BU	GN GY/PK	BN VT	WH BK
	M12 Output							
Byte 0 Byte 1	RD YE/BN	BU WH/YE	PK BN/GN	GY WH/GN	YE RD/BU	GN GY/PK	BN VT	WH BK

Diagnostic Indication

LED	Indication	Condition
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	sensor/system power supply
UL	green	actuator power supply
DIA	red	common indication for periphery faults



Degree of protection IP 67 Operating temperature range -10°C/+60°C

Weight 800 g (with 5 m cable)

Housing material

System/sensors

power supply Us 24 V DC Rated voltage 19-30 V DC Voltage range Power consumption 140 mA

Input power supply U_{S}

Voltage range min. (U_{System} – 1.5 V)

Sensor current 700 mA Short circuit proof yes Indication LED green

Input wiring Type 3 acc. to IEC 61131-2

Rated input voltage 24 V DC Channel type N.O. p-switching Number of digital channels max. 16

Output power supply \textbf{U}_{L} 24 V DC Rated voltage 19-30 V DC Voltage range

Reverse polarity protection yes/antiparallel diode

Indication LED green

Output wiring

0.5 A per channel Rated output current

Short circuit proof yes

Max. output current 6 A (3 A per group) Group 1 Channel 1-8 Group 2 Channel 9-16

Overload proof yes Number of digital channels max. 16 Channel type N.O. p-switching

Diagnostic

Periphery fault diagnosis for sensor short circuit, actuator short circuit, sensor low voltage detection

Designation

0942 UEM 780/... M






LioN-Link I/O Module with 16 Digital Outputs

0942 UEM 782



16 OUT

LioN-Link I/O module with 16 digital outputs, multipole cable interface to connect valve terminals, manual tool changing devices, IP20 terminal boxes



Bit Assignment

Bit	7	6	5	4	3	2	1	0
M12 Output								
Byte 0	RD	BU	PK	GY	YE	GN	BN	WH
Byte 1	YE/BN	WH/YE	BN/GN	WH/GN	RD/BU	GY/PK	VT	BK

Diagnostic Indication

LED	Indication	Condition
1/0	red red flashing green	wrong configuration/module exchanged not recognized by the BusHead online, communication with BusHead
Us	green	system power supply
U_{L}	green	actuator power supply
DIA	red	common indication for periphery faults

Pin Assignment

LioN-Link connection M12 Actuator/sensor connection M12 $1 = +24 \text{ V } (U_{L \, 1-8})$ 1 = Drain2 = 24 V Sensor/System $2 = +24 \text{ V } (U_{L 9-16})$ 3 = 0 V Sensor/System 3 = GND (0 V)4 = GND (0 V) 4 = Data + 5 = Data -5 = Earth

Degree of protection IP 67

Operating temperature range $-10^{\circ}\text{C}/+60^{\circ}\text{C}$

Weight 320 g (with 1 m cable)

Housing material PBT

System power supplyUsRated voltage24 V DCVoltage range19 – 30 V DCPower consumption40 mA

 $\begin{array}{ll} \textbf{Output power supply} & \textbf{U}_L \\ \textbf{Rated voltage} & 24 \text{ V DC} \\ \textbf{Voltage range} & 19-30 \text{ V DC} \end{array}$

Reverse polarity protection yes/antiparallel diode

Indication LED green

Output wiring

Rated output current 0.5 A per channel

Short circuit proof yes

Max. output current 6 A (3 A per group)
Group 1 Channel 1–8
Group 2 Channel 9–16

Overload proof yes
Number of digital channels max. 16
Channel type N.O. p-switching

Diagnostic

Periphery fault diagnosis for actuator short circuit

Designation

0942 UEM 782/... M






Power Distributor with 4 M12 Sockets

0941 UNC 601



LioN-Link power distributor, 4x M12 ports, 2 potential circuits, 10 m lead with 5x1 mm²



Power supply 1A- & 2A-M12	1B- & 2B-M12	Cable assignment	
1 = 24 V U _{LA} 2 = n.c. 3 = GND 0V U _{LA} 4 = n.c. 5 = Earth	1 = 24 V U _{LB} 2 = n.c. 3 = GND OV U _{LB} 4 = n.c. 5 = Earth	Function +24 V U _{LA} +24 V U _{LB} GND 0 V U _{LA} GND 0 V U _{LB} Earth	Wire color black 1 black ² black 3 black 4 green/yellow

Material

Housing PBT Contact holder PA

Contact M12 CuSn, pre-nickeled and 0.3 µm gold plated

threaded bush CuZn, nickel plated

0-ring

Operating temperature

-25°C/+70°C

Mechanical data

IP 67 Degree of protection

Only in the locked or bolted state with the corresponding counterparts or dust covers

Electrical data Type 3 acc. to IEC 61131-2

Rated current at 40°C 4 A/port, 12 A/module

Rated voltage 10-30V Operating indication LED green Insulation resistance $> 10^9 \ \Omega$ Degree of contamination 3

Included in

delivery/accessories Dust covers M12, attachable labels

Designation

0941 UNC 601/10M











Wiring Accessories BusHead





Wiring Accessories I/O Modules

LioN-Link connection, 5 poles	Designation			0942 UEM 65	0942 UEM 60/63
6	0935 253 10	CAN/DeviceNet signal cable, Thin Cable, M12		Q.	
	RST 5	Actuator/sensor cordset, M12 male connector with molded cable			
	RK(W)T 5	Actuator/sensor cordset, M12 female/female right angle connector with molded cable		6	
	RST 5-RKT 5	Actuator/sensor cordset, M12 male and female connector			
6	RSC(W) 5/9 RSC(W) 5/9	Field attachable connector, M12 male/ male right angle connector or M12 female/female right angle connector, with threaded joint		© (5)	
	0906 UTP 104	T-connector/splitter, 2-way, with mounting hole, M12 female connector with two M12 male connectors, 5-poles			
Actuator/sensor connection, 3 and 5 poles	s Designation			•	
	RSMV	Actuator/sensor cordset, M8 male connector with molded cable	•	•	
100 m	RSMC RSMCW	Field attachable connector, M8 male/male right angle connector, with threaded joint			
	RST	Actuator/sensor cordset, M12 male connector with molded cable			
	RSMV-RKM(WV) RST-RKM	Actuator/sensor cordset, M8/M12 male connector and M8/M12 female/female right angle connector			
	RSC RSCW	Field attachable connector, M12 male/male right angle connector, with threaded joint			
Power supply connection, 5 poles	Designation		•••		
	RKT 5 RKWT 5 RKT 5-226/ M P89	Actuator/sensor cordset, M12 female/female right angle connector with molded cable			
	0906 UTP 101	T-connector with M12 male/female connector, 5 poles			




Wiring Accessories I/O Modules



LioN-Link Configurator for Intermediate Supply

We provide a free calculation program to assist you in designing your LioN-Link network. This allows you to plan the necessary intermediate supplies accurately and select their optimum location within the network.



The table takes the following conditions into account:

Calculation of the voltage drop (in volts and percent) for each cable section between the designed Link modules of a Link branch, taking into account

- the Link cable length
- the Link cable cross section
- the Link module type
- the channel current load
- the module resultant current
- the total resultant current
- the Link connector M12

The program and instructions are available from the download portal at www.beldensolutions.com



Index

Index by designation

Designation	Order number	Page
0940 CSL 601	89975	20
0940 DSL 601	89974	22
0940 ESL 601	105689	24
0940 PSL 601	87058	14
0940 PSL 602	106172	16
0940 PSL 603	104873	18
0942 UEM 600	92356	30
0942 UEM 601	93201	32
0942 UEM 602	108105	48
0942 UEM 612	108106	50
0942 UEM 620	108053	42
0942 UEM 630	102076	34
0942 UEM 631	102080	36
0942 UEM 650	87040	26
0942 UEM 651	87043	28
0942 UEM 670	104872	40
0942 UEM 700	93199	44
0942 UEM 701	93198	46
0942 UEM 780/5 M	105165	52
0942 UEM 782/1 M	102840	54
0942 UEM 783	102163	38
0941 UNC 601/10 M	96720	56

Index by order number

Order number	Designation	Page
87040	0942 UEM 650	26
87043	0942 UEM 651	28
87058	0940 PSL 601	14
89974	0940 DSL 601	22
89975	0940 CSL 601	20
92356	0942 UEM 600	30
93198	0942 UEM 701	46
93199	0942 UEM 700	44
93201	0942 UEM 601	32
96720	0941 UNC 601/10 M	56
102076	0942 UEM 630	34
102080	0942 UEM 631	36
102163	0942 UEM 783	38
102840	0942 UEM 782/1 M	54
104872	0942 UEM 670	40
104873	0940 PSL 603	18
105165	0942 UEM 780/5 M	52
105689	0940 ESL 601	24
106172	0940 PSL 602	16
108053	0942 UEM 620	42
108105	0942 UEM 602	48
108106	0942 UEM 612	50

General Technical Information

Explanation of product features



UL approved



Highly resistant to oils, coolants, lubricants and emulsions



Highly resistant to vibrations and shocks

Important note

As a customer, you can expect our products to be in compliance with the latest technical standards. We therefore reserve the right to make design changes that may result in differences from the documented technical data.

If you have any special requirements or specifications, please consult our sales team. Our current terms and conditions of sale can be found on the Internet at www.beldensolutions.com



GLOBAL LOCATIONS

For worldwide sales and technical support, visit us at: www.lumberg-automation.com



CONTACT FOR LUMBERG AUTOMATION™ BRAND

Im Gewerbepark 2 58579 Schalksmühle Germany

Phone: +49-2355-5044-000 Fax: +49-2355-5044-333 www.beldensolutions.com lac-info@belden.com

CONTACT FOR HIRSCHMANN™ BRAND

Stuttgarter Straße 45-51 72654 Neckartenzlingen Germany

Phone: +49-7127-14-0 Fax: +49-7127-14-1970 www.beldensolutions.com inet-sales@belden.com

CONTACT FOR BELDEN® BRAND

Edisonstraat 9 5928 PG Venlo The Netherlands

Phone: +31-77-3878-555 Fax: +31-77-3878-488 www.beldensolutions.com venlo.salesinfo@belden.com